

# AELITEFLO™

## Light-Cured Flowable Microhybrid Composite



Highly Versatile and Uniquely Flexible

### VERSATILE


AELITEFLO is a light-cured composite with flow characteristics which make it ideal for Class V restorations, as well as Class III's and small Class IV's. Other uses of this material are as a liner for Class I and II restorations, pit and fissure sealants, the repair of marginal defects, small core build-ups, blocking out undercuts, porcelain repair, porcelain veneer cementation or as a flowable composite for bonding fibrous splints into place.

### FLEXIBLE

AELITEFLO was specially developed with a patented long chain monomer which supplements the conventional Bis-GMA resin to provide a more elastic composite. This allows restorations to flex with the tooth for improved marginal integrity and overall restoration longevity.

### UNIQUE BENEFITS

- Low modulus of elasticity microscopically bends with the natural flexure of the tooth to prevent de-bonding and marginal breakdown, especially in Class V restorations
- Flowable composite can be easily dispensed and injected into the preparation without dripping and slumping
- Uniform particle size is easily polished and stain resistant
- Glass-filler provides excellent wear resistance and strength



AELITEFLO's modulus of elasticity is much lower than natural tooth structure for ideal flexibility.

### CLINICAL SIGNIFICANCE

- Due to its elastic properties, AELITEFLO "bends with the tooth", leading to better retention. Excellent for abfraction lesions and Class V defects.

TO ORDER CALL: 1-800-BIS-DENT (1-800-247-3368)

[www.bisco.com](http://www.bisco.com)

Like us on:  

Rx Only

MC-3154AL



# AELITEFLO™

## Light-Cured Flowable Microhybrid Composite

### ORDERING INFORMATION

#### KIT CONTENTS

AELITEFLO INTRODUCTORY KIT

H-6701F

5 Syringes AELITEFLO (1.5g ea.) Shades A1, A2, A3.5, C2, and D3,  
Disposable Syringe Tips, Instructions/MSDS

#### REFILLS

AELITEFLO - 1 Syringe (1.5g), Disposable Syringe Tips, Instructions/MSDS

A1	H-671A1F	B3	H-672B3F
A2	H-671A2F	C2	H-673C2F
A2-OPAQUE	H-671A20F	C3	H-673C3F
A3	H-671A3F	D3	H-674D3F
A3.5	H-671A35F	OPAQUE WHITE	H-675OWF
A5	H-671A5F	TRANSLUCENT/INCISAL	H-675TIF
B1	H-672B1F		

### RELATED MATERIALS



SELECT HV™ ETCH  
35% Phosphoric Acid Etchant with  
Benzalkonium Chloride



ALL-BOND UNIVERSAL™  
Light-Cured Dental Adhesive



AELITEFLO™ LV  
Radiopaque Low Viscosity Composite



BISCO products are proudly  
made in the U.S.A.

TO ORDER CALL: 1-800-BIS-DENT (1-800-247-3368)



[www.bisco.com](http://www.bisco.com)

Not all products are available in all countries.

U.S. Patent: 5,865,623